




Connector Comparison Sheet

	Old Connector 3190-761 EZ-400-NMH-RA	New Connector 3190-2638 EZ-400-NMH-RA-X																																								
1. Materials&Plating	<table border="1"> <thead> <tr> <th></th> <th><u>Material</u></th> <th><u>Plating</u></th> <th><u>Thickness</u></th> </tr> </thead> <tbody> <tr> <td>1) Body</td> <td>Brass</td> <td>Silver</td> <td></td> </tr> <tr> <td>2) Center Contact</td> <td>Beryllium Copper</td> <td>Gold</td> <td></td> </tr> <tr> <td>3) Coupling nut</td> <td>Brass</td> <td>Silver</td> <td></td> </tr> <tr> <td>4) Ferruel</td> <td>Copper</td> <td>Silver</td> <td></td> </tr> </tbody> </table>		<u>Material</u>	<u>Plating</u>	<u>Thickness</u>	1) Body	Brass	Silver		2) Center Contact	Beryllium Copper	Gold		3) Coupling nut	Brass	Silver		4) Ferruel	Copper	Silver		<table border="1"> <thead> <tr> <th></th> <th><u>Material</u></th> <th><u>Plating</u></th> <th><u>Thickness</u></th> </tr> </thead> <tbody> <tr> <td>1) Body</td> <td>Brass</td> <td>Albaloy</td> <td>>79μ"(2μm)</td> </tr> <tr> <td>2) Center Contact</td> <td>Beryllium Copper</td> <td>Gold</td> <td>>50μ"(1.27μm)</td> </tr> <tr> <td>3) Coupling nut</td> <td>Brass</td> <td>Albaloy</td> <td>>79μ"(2μm)</td> </tr> <tr> <td>4) Ferruel</td> <td>Copper</td> <td>Albaloy</td> <td>>79μ"(2μm)</td> </tr> </tbody> </table>		<u>Material</u>	<u>Plating</u>	<u>Thickness</u>	1) Body	Brass	Albaloy	>79μ"(2μm)	2) Center Contact	Beryllium Copper	Gold	>50μ"(1.27μm)	3) Coupling nut	Brass	Albaloy	>79μ"(2μm)	4) Ferruel	Copper	Albaloy	>79μ"(2μm)
	<u>Material</u>	<u>Plating</u>	<u>Thickness</u>																																							
1) Body	Brass	Silver																																								
2) Center Contact	Beryllium Copper	Gold																																								
3) Coupling nut	Brass	Silver																																								
4) Ferruel	Copper	Silver																																								
	<u>Material</u>	<u>Plating</u>	<u>Thickness</u>																																							
1) Body	Brass	Albaloy	>79μ"(2μm)																																							
2) Center Contact	Beryllium Copper	Gold	>50μ"(1.27μm)																																							
3) Coupling nut	Brass	Albaloy	>79μ"(2μm)																																							
4) Ferruel	Copper	Albaloy	>79μ"(2μm)																																							
2. Dimension&Outline																																										
3. Installation	Need Braid Trim	No Braid Trim																																								

4. Test Curve



* The test curve is based on the assembly 1m cable with 2 connectors on each end.